

# JAM INJECTION MACHINE

SERIES ED AND FS

SOFT FILLING  
WITH EXACT DOSAGE



Model ED-1



## SMOOTHLY FILLING WITH DIFFERENT TYPES OF FILLINGS

The container with 13,5 litre capacity can be replaced by another at any time. In this way the filling mixture can be changed very simple. Also fillings with granulation up to 2 mm (e.g. small pips) can be used. The tough design of the pump is able to pump this without plugging.

## EASE OF USE

Easy handling by ergonomic mounted needles. While keeping the pastries the filling process is initiated by pressing the bottom plate. In this way up to 60 pastries each minute can be filled softly.



## INDIVIDUAL QUANTITY OF FILLINGS

The filling quantity can be adjusted stepless between 5 and 30 g. To do this just a knurled screw has to be turned and fixed in the right position.



## QUICK CLEANING

For cleaning purpose the single parts which has contact with the filling mixture can be disassembled and removed easily. No special tools are required.





## MODELS AVAILABLE

Electric driven  
Type ED-1

Pneumatic driven  
Type FS-1

## STANDARD FEATURES

Complete stainless steel construction

Two 8 mm needles

One container for filling mixture with sealing plug and removable cover.

Type ED-1 is equipped with 230 V two-pin grounded plug

Type FS-1 is equipped with 1/8"- compressed air supply.

## OPTIONAL FEATURES at additional cost

Needles sizes from 6 to 10 mm

Additional containers for different mixtures

Container rack

Mobile underframe or mobile cabinet base.

Compressor cabinet with compressor unit for Type FS-1

## TECHNICAL DATA:

	ED-1	FS-1
Container capacity	13,5 litre	3,5 litre
Filling capacity	5 to 30 g	5 to 30 g
Width	380 mm	380 mm
Height	400 mm	400 mm
Depth	710 mm	710 mm
Electrical input	0,6 kW	-
Voltage	230 V	-
Airpressure*	-	8 bar

\* dry air

Specifications subject to change without notice